



Polish this face to high reflectivity

NOTES

1. Adjust dimensions for fit to PFS15031. OD's on PFS15032 should be 0.010 smaller than ID's on PFS15031. Thickness 0.185 on PFS15032 should be 0.003 smaller than depth of corresponding hole on PFS15031.

2. Anodize black, masking polished face

1	1	PFS15032
ITEM	QTY	DESCRIPTION
Bill of Material		

THE OBSERVATORIES OF THE CARNEGIE INSTITUTION OF WASHINGTON 813 Santa Barbara Street Pasadena, CA 91101					
MATERIAL		UNLESS OTHERWISE SPECIFIED			
Al 6061-T6		FRACTIONAL	DECIMAL	ANGULAR	
		+/- 1/32	.XX +/- 0.01	+/- 0.1 DEG	
EST WEIGHT		.XXX +/- 0.002 GOAL			
1.0 oz		.XXX +/- 0.005 REQD			
SCALE		BREAK SHARP EDGES		MACHINED SURFACES 125 $\sqrt{\text{in}}$	
1:1		ALL DIMENSIONS IN INCHES		P lanet F nder S pectrograph CCD Main Head Plug	
DWN	CRANE	7/17/2007			
APVD		SHEET	DRAWING NUMBER		REV
	BY	DATE	A PFS15032		SHT 1 OF 1